



Discover more details and matching accessories online!

Reliable material thickness gauge for daily use

Features

- External measuring head for difficult-to-access measuring points
- Selectable measuring units: mm, inch
- Auto-Power-Off
- Base plate for adjustment included
- Scope of delivery: Operating instructions, batteries, external measuring head (ø 8 mm) and ultrasound contact gel
-  Delivered in a robust carrying case
- TB 200-0.1US-RED: Can only analyse these materials: cast iron, aluminium, copper, brass, zinc, quartz glass, polyethylene, PVC, grey cast iron, nodular cast iron, steel

Technical data

- Measuring precision: 0,5 % of [Max]
- Overall dimensions W×D×H 161×69×32 mm
- Battery operation, batteries standard (4×1.5 V AA)
- Net weight approx. 0,30 kg

STANDARD



OPTION



Model	Measuring range	Readout	Sensor	Sound velocity	Price excl. of VAT ex works €	Option
						Factory calibration certificate
SAUTER	mm	[d] mm		m/sec		KERN
TB 200-0.1US	1,5 – 200	0,1	5 MHz ø 8 mm	500 – 9999	405,-	961-113
TB 200-0.1US-RED	1,5 – 200	0,1	5 MHz ø 8 mm	500 – 9999	345,-	961-113