

# KERN TB 2000-0.1F.

Ihr praktisches Arbeitsinstrument für den robusten Alltagseinsatz



## Construction

Cable length:	1 m
Casing material:	Plastic
Overall dimensions mounted (WxDxH):	161 x 69 x 32 mm

## Measuring system

Measuring range [Max]:	100 x 2000 $\mu\text{m}$
Minimal base thickness:	300 $\mu\text{m}$
Precision (of [Max]):	5 %
Precision (Offset-Accur):	1 %
Readout [d]:	0 x 0,001 mm
Smallest sample surface, convex (radius):	3 mm
Smallest sample surface, flat (radius):	6 mm
Smallest sample surface,concave (radius):	5 cm
Weighing units:	$\mu\text{m}$ inch (mil)

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

## Service

ISO calibration certificate:	961-110
------------------------------	---------

## Category

Brand:	Sauter
Category:	Coating thickness
Product Group:	Coating thickness gauge

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	260 g
Shipping method:	Parcel service