



Discover more details and matching accessories online!

Ideal for food industry, thanks to its IP65 protection and special checkweighing display, verification optional

Features

- Ideal for the increased hygienic requirements in the food industries
- Your support in a HACCP-compliant quality system
- 1 Protection against dust and water splashes IP65 (only when using rechargeable battery pack)
- Very fast display: steady weight values within 2 s
- 2 Second display on the back of the balance
- Compact size
- 3 Innovative weighing with tolerance range: The colour of the display changes depending on the weight (too light/ok/too heavy) and is an aid to help with portioning, dosing and grading

- Thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations
- Recessed grips on the underside of the scale for easy transportation
- Protective working cover included with delivery

Technical data

- Large backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, W×D 263×203 mm
- Overall dimensions W×D×H 286×316×126,5 mm
- Net weight approx. 3,2 kg
- Permissible ambient temperature -10 °C/40 °C

STANDARD



OPTION



FACTORY



1

IP 65

1 DAY

DAkks

WTB-NM

Model	Weighing capacity	Readability	Verification value	Minimal load	Options	
					Verification	Calibr. Certificate
KERN	[Max] kg	[d] g	[e] g	[Min] g	 KERN	DAkks accr. KERN
WTB 1K-4N	1,5	0,2	-	-	-	963-127
WTB 3K-4N	3	0,5	-	-	-	963-127
WTB 6K-3N	6	1	-	-	-	963-128
WTB 10K-3N	15	2	-	-	-	963-128
WTB 30K-3N	30	5	-	-	-	963-128
Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.						
WTB 1K-4NM	1,5	0,5	0,5	10	965-227	963-127
WTB 3K-3NM	3	1	1	20	965-227	963-127
WTB 6K-3NM	6	2	2	40	965-228	963-128
WTB 10K-3NM	15	5	5	100	965-228	963-128
WTB 30K-2NM	30	10	10	200	965-228	963-128

1 ONLY WHILE STOCKS LAST