



**NOTE:**

1. CABLE,UL2725, 2.0 AL+B-FOIL,28AWG\*1P+24AWG\*2C,OD: 5.0MM,PVC JACKET
2. LENGTH: L
3. CONNECTOR: USB4P(A)\*1,USB4P(B)\*1(WHITE INSULATOR),ALIKE MOLDING
4. CONTACTS:GOLD FLASH 1 MICRON
5. CONTACTS:



WHITE/GREEN...28AWG , RED/BLACK...24AWG

6. OPEN/SHORT TEST: 100% TEST.  
INSULATION: 2M.
7. COLOR CHART  
 TRANSPARENT: Pantone 428C  
 GRAY: Pantone Coolgray 7C  
 RED: Pantone 1945C  
 BLUE: Pantone 3015C  
 BLACK: Pantone black 6C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF INTRACOM Asia Co., Ltd. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF INTRACOM Asia Co., Ltd.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: ±1°

TOLERANCE (INCH)		TOLERANCE (MM)	
x	±0.02"	x	±0.5mm
x.x	±0.01"	x.x	±0.25mm
x.xx	±0.005"	x.xx	±0.15mm
x.xxx	±0.005"	x.xxx	±0.10mm

<b>安達康股份有限公司</b>			
<b>USB 2.0 CABLE</b>		APPD	
		Check	
CUSTOMER:		Drawn	Date 16/06/05
CUSTOMER P/N:		Unit	mm Projection
ICT P/N:		Scale	1:1 Size <b>A4</b>
DWG NO: <b>ICML 06-08-15-03</b>		Sheet	1 of REV. <b>A</b>