



## Hi-Speed USB B Device Cable

USB 2.0, Type-A Male to Type-B Male, 480 Mbps, 3 m (10 ft.), Black

Part No.: [333382](#)

EAN-13: 0766623333382 | UPC: 766623333382

---

Connect with confidence

MANHATTAN Hi-Speed USB 2.0 Device Cables easily connect USB peripherals and accessories with desktop and notebook computers. Ideal for use with many USB external enclosures, hubs and other hot-swap, Plug and Play devices, MANHATTAN Hi-Speed USB 2.0 Device Cables support data transfer rates up to 480 Mbps on Windows and Mac systems for fast, reliable transmissions. Gold-plated contacts, shielding and fully molded boots with strain relief help provide dependable connections, maximum conductivity and minimal data loss with reduced EMI interference.

### Features:

- USB 2.0 Standard-A male to USB 2.0 Standard-B male
- Connects a Hi-Speed USB device to a Hi-Speed USB hub or computer
- Supports speeds of up to 480 Mbps
- Hi-Speed USB for ultra-fast data transfer rates with zero data degradation
- Lifetime Warranty

### Specifications:

#### Standards and Certifications

- UL 2725
- USB 2.0

#### Connectors

- (1) USB 2.0 Standard-A male
- (1) USB 2.0 Standard-B male

- Gold plated
- Molded PVC boot

#### Cable

- 28 AWG conductors
- Shielded
- Withstanding voltage: 300 V DC 10 ms
- Insulation resistance: 5 MOhms
- Contact resistance: 10 Ohms
- Thermal plastic casing

#### Package Contents

- Hi-Speed USB Device Cable

