

Product Specification (Spec)

Plugs, adaptor	KVB8323 201 KVB8323 221 KVB8323 531 KVB8323 602 KVB8323 941	written: released:	AST	20.03.2009
----------------	---	-----------------------	-----	------------

Mechanical data:

size Größe	mm material, colour	20 mm ± 2 mm
material Material		brass
Colour (coating) Farbe (Beschichtung)		nickel coated
temperature range Temperatur	installation operating storage	-5°C – +40°C -20°C – +50°C -20°C – +50°C

Electrical Data:

attenuation Dämpfung	dB	max. 1 dB
screening factor Schirmungsmaß	30 – 2400 MHz	n.a.

Other requirements:

appearance	clean, shiny, smooth surface
packing	bulk, individual
individual packaging (D x W x H)	
Inner packing (D x W x H)	

Foto / drawing / sketch:

