

# Cable - FLK 40/EZ-DR/ 200/KONFEK - 2289010

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round cable sets, with two 40-pos. socket strips (1:1 connection), also for use with Siemens SIMATIC® S5-95U and 100U (32 x digital IN/OUT), cable length: 2 m

The illustration shows a 50-pos. version

## Product Features

- Unshielded

## Key commercial data

package_quantity	1
GTIN	4017918057404

## Technical data

### General

Nominal voltage $U_N$	< 50 V AC
Nominal voltage $U_N$	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega$ /m
Length of cable	2 m
Single wire, cross section	0.14 mm <sup>2</sup>
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	9.9 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no
Outer sheath, material	PVC
External sheath, color	Gray RAL 7035

### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

# Cable - FLK 40/EZ-DR/ 200/KONFEK - 2289010

## Technical data

### Connector, module side

<b>Number of positions</b>	40
<b>Connectors</b>	IDC/FLK socket strip (2.54 mm)
<b>Number of plugs</b>	1

### Connector, controller side

<b>Number of positions</b>	40
<b>Connectors</b>	IDC/FLK socket strip (2.54 mm)
<b>Number of plugs</b>	1

### Supported controller

<b>Control</b>	SIEMENS S5-95U/ET100U S5-100U/ET200U
----------------	--------------------------------------

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000237
<b>ETIM 3.0</b>	EC000237
<b>ETIM 4.0</b>	EC000237
<b>ETIM 5.0</b>	EC000237

### UNSPSC

<b>UNSPSC 6.01</b>	26121620
<b>UNSPSC 7.0901</b>	26121620
<b>UNSPSC 11</b>	26121620
<b>UNSPSC 12.01</b>	26121620
<b>UNSPSC 13.2</b>	26121620

## approvals

---

UL Recognized / cUL Recognized / GOST / cULus Recognized /

---

### Approval details


## Cable - FLK 40/EZ-DR/ 200/KONFEK - 2289010

approvals

UL Recognized 

cUL Recognized 

GOST 

cULus Recognized 

Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>