

D-SUB pressure nut - VS-PG11 (5-10) - 1688104

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



D-SUB cap nut with line seal, for conductor diameter of 5 mm ... 10 mm, for sleeve housing VS-15-...

Key commercial data

package_quantity	5
GTIN	4017918182281

Technical data

Dimensions

External cable diameter	5 mm ... 10 mm
--------------------------------	----------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
--	------------------

General

Color	gray
Type of the screw connection	Pg11
Housing material	PA
Seal material	Neoprene
Inflammability class according to UL 94	V0

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261203
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437

D-SUB pressure nut - VS-PG11 (5-10) - 1688104

classifications

ETIM

ETIM 5.0	EC002355
-----------------	----------

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing

D-SUB cap nut

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>