

# Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 6 m

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918893071

## Technical data

### General

<b>Nominal voltage <math>U_N</math></b>	125 V AC/DC
<b>Max. current carrying capacity per path</b>	2 A
<b>Max. conductor resistance</b>	$\leq 0.09 \Omega/m$
<b>Length of cable</b>	6 m
<b>Single wire, cross section</b>	0.25 mm <sup>2</sup>
<b>AWG</b>	24
<b>External diameter</b>	9 mm
<b>Shielding</b>	yes
<b>Shielding</b>	Tinned copper-braided shield, approx. 85% covering
<b>Insertion/withdrawal cycles</b>	> 200

### Environmental conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C
<b>Flame resistance</b>	IEC 60332-1

### Connector, module side

<b>Number of positions</b>	15
<b>Connectors</b>	D-SUB socket strip
<b>Number of plugs</b>	1

### Connector, controller side

<b>Number of positions</b>	15
<b>Connectors</b>	D-SUB pin strip
<b>Number of plugs</b>	1

# Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

## classifications

### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

### ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000830


### UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

## approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

### Approval details



## Cable - CABLE-D15SUB/B/S/600/KONFEK/S - 2302117

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>