

Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE SLIM LINE, with screw connection and D-subminiature pin strip, for assembly at a right angle on NS 35/7.5, 15 positions

The illustration shows the version UM 25-D 9SUB/B/FRONT/Q



Key commercial data

package_quantity	1
GTIN	4017918086244

Technical data

Dimensions

Width	25 mm
Height	147 mm
Depth	45 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	15
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	IEC 60664 A
Standards/regulations	DIN VDE 0110
Standards/regulations	DIN VDE 0160 (in parts)
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV

Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

Technical data

General

Rated insulation voltage	125 V
---------------------------------	-------

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	15

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

approvals

GOST /

Approval details



accessories

System cable

CABLE-D15SUB/B/S/ 50/KONFEK/S - 2302052



CABLE-D15SUB/B/S/100/KONFEK/S - 2302065



CABLE-D15SUB/B/S/150/KONFEK/S - 2302078



CABLE-D15SUB/B/S/200/KONFEK/S - 2302081



Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

accessories

CABLE-D15SUB/B/S/300/KONFEK/S - 2302094



CABLE-D15SUB/B/S/400/KONFEK/S - 2302104



CABLE-D15SUB/B/S/600/KONFEK/S - 2302117



CABLE D-SUB-S/.../.../... - 2302340



CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE-D-15SUB/F/OE/0,25/S/0,5M - 2926085



Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

accessories

CABLE-D-15SUB/F/OE/0,25/S/1,0M - 2926098



CABLE-D-15SUB/F/OE/0,25/S/1,5M - 2926108



CABLE-D-15SUB/F/OE/0,25/S/2,0M - 2926111



CABLE-D-15SUB/F/OE/0,25/S/3,0M - 2926124



CABLE-D-15SUB/F/OE/0,25/S/4,0M - 2926137



Interface module - UM 25-D15SUB/S/FRONT/Q - 2959599

accessories

CABLE-D-15SUB/F/OE/0,25/S/6,0M - 2926140



CABLE-D-15SUB-F-OE-0,25-S/... - 2900905



Drawings

Circuit diagram

