

Half screw connection - VC-M-KV-PG16(7-10,5) - 1853971

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Half screw connection Pg16, made of metal, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 7 - 10.5

Key commercial data

package_quantity	5
GTIN	4017918146320

Technical data

Dimensions

Wrench size, union nut	24 mm
External cable diameter	7 mm ... 10.5 mm

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Cable seal material	TPE
Thread type on seal side	Pg16
Tightening torque, union nut	7.50 Nm

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

Half screw connection - VC-M-KV-PG16(7-10,5) - 1853971

classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

approvals

GOST /

Approval details



accessories

VC-M-KV-PG21- 0 - 1854983

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>