

Interface module - UMK- EC38/38-XOL - 2976284

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, for ELCO connector, for mounting on NS 35/7.5 or NS 32, with pin strip 8016 left, no. of positions 38



Key commercial data

package_quantity	1
GTIN	4017918089313

Technical data

Dimensions

Width	101.5 mm
Height	77 mm
Depth	58.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Nominal voltage U_N	25 V AC
Nominal voltage U_N	60 V DC
Max. current carrying capacity per branch	2 A
Max. total current of all branches	76 A
Number of positions	38
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	0.8 kV
Rated insulation voltage	85 V

Connection data for connection 1

Connection name	PCB connection
-----------------	----------------

Interface module - UMK- EC38/38-XOL - 2976284

Technical data

Connection data for connection 1

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	ELCO connection
Number of connections	1
Connection method	ELCO connector
Number of positions	38

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC


UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Interface module - UMK- EC38/38-XOL - 2976284

approvals

GOST /

Approval details



Drawings

Dimensioned drawing

