

Shield connection clamp - HC-D 4-BU-2BUS - 1886139

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shield connection, for two shielded cables, incl. two loose socket crimp contacts for PROFIBUS cables.

Key commercial data

package_quantity	1
GTIN	4017918818401

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
--	------------------

General

Note	For HC-D40-, HC-D64-, HC-M-12- contact carriers
-------------	---

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501

Shield connection clamp - HC-D 4-BU-2BUS - 1886139

classifications

UNSPSC

UNSPSC 13.2	31261501
-------------	----------

approvals

GOST /

Approval details



accessories

Assembly tool

CK1,6/2,5-MWZ - 1676734



VC-EW 1,6 - 1884869



Crimping tool

CRIMPFOX-1,6/2,5-ED-4,0 - 1687419



Drawings

Shield connection clamp - HC-D 4-BU-2BUS - 1886139

Dimensioned drawing

