

Cable - CABLE-D25SUB/B/S/150/KONFEK/S - 2302146

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 1.5 m

The illustration shows a 15-position version

Key commercial data

package_quantity	1
GTIN	4017918893101

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Length of cable	1.5 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	10.5 mm
Shielding	yes
Shielding	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Number of positions	25
Connectors	D-SUB socket strip
Number of plugs	1

Connector, controller side

Number of positions	25
Connectors	D-SUB pin strip
Number of plugs	1

Cable - CABLE-D25SUB/B/S/150/KONFEK/S - 2302146

Technical data

Supported controller

Control	ABB S800 I/O
- suitable I/O card	DI810
- suitable I/O card	DI811
- suitable I/O card	DI814
- suitable I/O card	DI830
- suitable I/O card	DI831
- suitable I/O card	DI840
- suitable I/O card	DI885
- suitable I/O card	DO810
- suitable I/O card	DO814
- suitable I/O card	DO840
- suitable I/O card	DP820
- suitable I/O card	AI810
- suitable I/O card	AI820
- suitable I/O card	AI830
- suitable I/O card	AI835
- suitable I/O card	AI845
- suitable I/O card	AO810
- suitable I/O card	AO820

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000830

UNSPSC


UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Cable - CABLE-D25SUB/B/S/150/KONFEK/S - 2302146

approvals


UL Recognized / cUL Recognized / GOST / cULus Recognized /

Approval details

UL Recognized 

cUL Recognized 

GOST 

cULus Recognized 

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>