

# Display panel system VARIO® WALL 10

|                |                  |                        |               |
|----------------|------------------|------------------------|---------------|
| Article number | 556700           | Sales unit quantity    | 1 Set         |
| Colour         | Assorted colours | Sales unit EAN         | 4005546502571 |
| Packaging unit | 1 set            | Packing weight (gross) | 970 G         |
| Base EAN       | 4005546502571    | Country of origin      | DE            |



## Logos and awards



## Product description

- Complete display panel set for wall applications
- Wall bracket with 10 SHERPA® display panels in A4 format (2 units each in black, red, yellow, green and dark blue)
- Polypropylene display panels with coloured profile frame and low-reflection film suitable for scanners
- Incl. tabs with blank insert sheets for labelling the display panels
- Simple wall mounting
- Practical pivot mechanism for simple replacement of the displays
- 5-year warranty

## Product features

|                   |     |
|-------------------|-----|
| Outer width (mm)  | 390 |
| Outer height (mm) | 325 |

556700\_PDS\_DURABLE\_en\_GB.pdf | 2025-02-03 03:16

1/2

DURABLE Hunke & Jochheim GmbH & Co. KG  
Westfalenstraße 77 – 79 · 58636 Iserlohn · Germany  
Phone +49 (0) 2371 662 0 · Fax +49 (0) 2371 662 221  
Mail [durable@durable.de](mailto:durable@durable.de) | [durable.de](http://durable.de)

The statements contained herein are for informational purposes only and are true and accurate to the best of our scientific and technical knowledge. This information does not constitute a guarantee or warranty, express or implied, nor does it establish a legally valid contractual relationship. It is the customer's responsibility to determine the suitability of this product for the customer's intended use. DURABLE does not assume any liability for the customer's use of this product or the information contained herein.



# Display panel system VARIO® WALL 10

|                                         |                            |
|-----------------------------------------|----------------------------|
| Outer depth / length                    | 260 mm                     |
| Filling quantity / Filling quantity for | 10 Display panel(s)        |
| Format / Format for                     | A4                         |
| Orientation Format                      | Portrait                   |
| Brand                                   | DURABLE                    |
|                                         |                            |
| Inner display panel width (mm)          | 210                        |
| Inner display panel height (mm)         | 297                        |
| Set includes display panels             | Yes                        |
| Rotate / Swivel amounts                 | No                         |
| Adjustable reading angle                | No                         |
| Extendable                              | No                         |
| Opening for documents                   | Top                        |
| Tabs with blank labels included         | Yes                        |
| Antibacterial                           | No                         |
| Warranty                                | 5 years                    |
| Product features relating to documents  | Can be scanned, anti-glare |
| Base / mount type                       | Wall mount                 |