

Socket insert - VS-SI-SD-DE-G - 1656518

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ground contact socket, exclusively for service interface order no. 1656482 and 1656495, plastic, for Germany, yellow

Key commercial data

package_quantity	1
GTIN	4046356029889

Technical data

Mechanical characteristics

Connection method	Screw connection
Conductor cross section	2.5 mm ²
Connection cross section AWG	14
Color	yellow

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Housing material	PA

Electrical characteristics

Rated voltage (III/3)	250 V
Rated current	16 A

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

Socket insert - VS-SI-SD-DE-G - 1656518

classifications

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC000125
ETIM 4.0	EC000125
ETIM 5.0	EC000125

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

GOST /

Approval details

 GOST

Drawings

Dimensioned drawing

Socket insert

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>