

# Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5 m

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918057640

## Technical data

### General

<b>Nominal voltage U<sub>N</sub></b>	< 50 V AC
<b>Nominal voltage U<sub>N</sub></b>	60 V DC
<b>Max. current carrying capacity per path</b>	1 A
<b>Max. conductor resistance</b>	0.16 Ω/m
<b>Length of cable</b>	5 m
<b>Single wire, cross section</b>	0.14 mm <sup>2</sup>
<b>AWG</b>	26
<b>Conductor construction: Number of litz wires:</b>	7
<b>Single wire, material</b>	Cu tin-plated
<b>External diameter</b>	10.3 mm
<b>Cable, preassembly</b>	Insulation displacement, IEC 60352-4/DIN EN 60352-4
<b>Shielding</b>	no
<b>Outer sheath, material</b>	PVC
<b>External sheath, color</b>	Gray RAL 7035

### Environmental conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C
<b>Flame resistance</b>	IEC 60332-1
<b>Resistance to oil</b>	DIN VDE 0472 Part 803, test type B
<b>Gasoline resistance</b>	Against occasional splashes

### Connector, module side

<b>Number of positions</b>	50
<b>Connectors</b>	IDC/FLK socket strip (2.54 mm)
<b>Number of plugs</b>	1

# Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586

## Technical data

### Connector, controller side

<b>Number of positions</b>	50
<b>Connectors</b>	IDC/FLK socket strip (2.54 mm)
<b>Number of plugs</b>	1

### Supported controller

<b>Control</b>	SIEMENS S7-300 / ET 200 M
- suitable I/O card	CPU 313C
- suitable I/O card	CPU 313C-2DP
- suitable I/O card	CPU 313C-2PtP
- suitable I/O card	CPU 314C-2DP
- suitable I/O card	CPU 314C-2PtP
- suitable I/O card	6ES7 321-1BL00-0AA0
- suitable I/O card	6ES7 322-1BL00-0AA0
- suitable I/O card	6ES7 322-8BH01-0AB0
- suitable I/O card	6ES7 323-1BL00-0AA0
- suitable I/O card	6ES7 326-1BK02-0AB0
- suitable I/O card	6ES7 326-1RF00-0AB0
- suitable I/O card	6ES7 326-2BF01-0AB0
- suitable I/O card	6ES7 326-2BF10-0AB0
- suitable I/O card	6ES7 331-1KF01-0AB0
- suitable I/O card	6ES7 331-7NF00-0AB0
- suitable I/O card	6ES7 331-7NF10-0AB0
- suitable I/O card	6ES7 331-7PF01-0AB0
- suitable I/O card	6ES7 331-7PF11-0AB0
- suitable I/O card	6ES7 332-5HF00-0AB0
- suitable I/O card	6ES7 350-2AH01-0AE0
- suitable I/O card	6ES7 357-4AH01-0AE0
<b>Control</b>	SIEMENS S7-400
- suitable I/O card	6ES7 421-1BL01-0AA0
- suitable I/O card	6ES7 421-7BH01-0AB0
- suitable I/O card	6ES7 421-7DH00-0AA0
- suitable I/O card	6ES7 422-1BL00-0AA0
- suitable I/O card	6ES7 422-7BL00-0AB0
- suitable I/O card	6ES7 431-0HH0-0AB0
- suitable I/O card	6ES7 431-1KF00-0AB0
- suitable I/O card	6ES7 431-1KF10-0AB0
- suitable I/O card	6ES7 431-1KF20-0AB0
- suitable I/O card	6ES7 431-7KF00-0AB0
- suitable I/O card	6ES7 431-7KF10-0AB0
- suitable I/O card	6ES7 431-7QH00-0AB0
- suitable I/O card	6ES7 432-1HF00-0AB0
<b>Control</b>	Schneider Electric MODICON TSX QUANTUM

## Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586

### Technical data

#### Supported controller

- suitable I/O card	DDI 353
- suitable I/O card	DDI 841
- suitable I/O card	DDI 853
- suitable I/O card	DAI 340
- suitable I/O card	DAI 353
- suitable I/O card	DAI 440
- suitable I/O card	DAI 453
- suitable I/O card	DDO 353
- suitable I/O card	DDM 390
- suitable I/O card	ACI 030
- suitable I/O card	ACI 040
- suitable I/O card	ATI 030
- suitable I/O card	ARI 030
- suitable I/O card	AVI 030
- suitable I/O card	ACO 020
- suitable I/O card	ACO 130
- suitable I/O card	AVO 020
- suitable I/O card	EHC 105
- suitable I/O card	EHC 202
<b>Control</b>	ALLEN-BRADLEY ControlLogix
- suitable I/O card	1756-IA16I
- suitable I/O card	1756-IB16D
- suitable I/O card	1756-IB16I
- suitable I/O card	1756-IB32
- suitable I/O card	1756-IH16I
- suitable I/O card	1756-OB32
- suitable I/O card	1756-IF8
- suitable I/O card	1756-IF16
- suitable I/O card	1756-HSC
- suitable I/O card	1756-M02AE
<b>Control</b>	ALLEN-BRADLEY PLC 5
- suitable I/O card	1771 IBN
- suitable I/O card	1771 OBN
<b>Control</b>	HONEYWELL PlantScape
- suitable I/O card	TC-IDK 161
- suitable I/O card	TC-IDX 161
- suitable I/O card	TC-IDJ 161
- suitable I/O card	TC-IDD 321
- suitable I/O card	TC-ODD 321
- suitable I/O card	TC-IAH 161
<b>Control</b>	ALLEN-BRADLEY SLC 500

# Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586

## Technical data

### Supported controller

- suitable I/O card	1746 OA16
- suitable I/O card	1746 OW16

## classifications

### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

### ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

### UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620


## approvals

---

UL Recognized / cUL Recognized / GOST / cULus Recognized /

---

### Approval details



## Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586

approvals



Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>