RJ45 coupling - VS-PPC-J-1-RJ45-MNBK - 1405183

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



RJ45 push-pull coupling

RJ45 push-pull coupling, IP67, metal, CAT5e, with protective cover, color: Nickel-plated

Ethernet PROFINET sercos the automation bus

Key commercial data

package_quantity	1
GTIN	4046356332774

Technical data

Mechanical characteristics

Number of positions	8
Connection profile	RJ45 8(8)
Cable exit	Straight
Color	silver

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP67

Material data

Housing material	Zinc die-cast
Contact material	Copper alloy

Electrical characteristics

Rated voltage (III/3)	50 V
Rated surge voltage	≥ 1 kV
Rated current	1 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701

RJ45 coupling - VS-PPC-J-1-RJ45-MNBK - 1405183

classifications

eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM


ETIM 3.0	EC001134
ETIM 4.0	EC001134
ETIM 5.0	EC001134

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing



RJ45 push-pull coupling

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com