

Grommet - VS-ASI-FC-SEAL-HP - 1400374

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



End sealing for AS-Interface flat-ribbon conductor, can be used on both sides, IP67 degree of protection:



Key commercial data

package_quantity	10
GTIN	4046356495080

Technical data

Mechanical characteristics

Color	black
Tightening torque, union nut	2.00 Nm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Degree of protection	IP67

Material data

Material	PA
Seal material	NBR

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
----------	----------

Grommet - VS-ASI-FC-SEAL-HP - 1400374

classifications

ETIM

ETIM 4.0	EC001181
ETIM 5.0	EC001181

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing

