

FO connecting cable - VS-PC-2XPOF-980-SCRJ/ SCRJ-5 - 1656479

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Assembled FO cable, break-out cable, polymer fiber 980/1000 µm, SCRJ/IP20 on SCRJ/IP20, for installation inside the control cabinets, the conductor is suitable for the UV-protected outside insert, length: 5 m



Key commercial data

package_quantity	1
GTIN	4046356029841

Technical data

Mechanical characteristics

Number of positions	2
Connection profile	SCRJ according to DIN EN 50377-6-1
Fiber	980/1000 µm
Number of fibers	2.00
Insertion/withdrawal cycles	≥ 1000
Type of cable	Break-out cable
Length of cable	5 m

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Degree of protection	IP20

Material data

Housing material	PBT
Outer sheath, material	PE
External sheath, color	black
Ferrule holder color	Blue

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701

FO connecting cable - VS-PC-2XPOF-980-SCRJ/ SCRJ-5 - 1656479

classifications

eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27061003
eCl@ss 7.0	27061003
eCl@ss 8.0	27061003

ETIM


ETIM 2.0	EC000764
ETIM 3.0	EC001263
ETIM 4.0	EC001263
ETIM 5.0	EC000830

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings


Dimensioned drawing



SCRJ connector, POD, IP20


FO connecting cable - VS-PC-2XPOF-980-SCRJ/ SCRJ-5 - 1656479

Dimensioned drawing



SCRJ connector, POD, IP20


Schematic diagram



Pin assignment plug SCRJ

FO connecting cable - VS-PC-2XPOF-980-SCRJ/ SCRJ-5 - 1656479

Schematic diagram



Pin assignment plug SCRJ

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>