

D-SUB pressure nut - VS-M20 (5-13) - 1652127

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



D-SUB cap nut with line seal, for conductor diameter of 5 mm ... 13 mm, for sleeve housing VS-25-...

Key commercial data

package_quantity	5
GTIN	4017918917111

Technical data

Dimensions

External cable diameter	5 mm ... 13 mm
--------------------------------	----------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
--	------------------

General

Color	gray
Type of the screw connection	M20
Housing material	PA
Seal material	Neoprene
Inflammability class according to UL 94	V0

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441

D-SUB pressure nut - VS-M20 (5-13) - 1652127

classifications

ETIM

ETIM 5.0	EC002355
-----------------	----------

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Drawings

Dimensioned drawing

