





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AF	50		T	REVISED PER ECR-13-004343	30JUL13	KH
						KR

- 1 FITS 0.81±0.025 X 6.35 [.032±.001 X .250] TAB
- 2 WIRE SIZE: 0.3–0.9mm² [22–18 AWG], STRANDED ONLY.
STRIP LENGTH 7.94 [.312]
- 3 INSULATION SIZE: 4.19 [.165] MAX DIA.
- 4 SUPPLIED AS LOOSE PIECE.



TYPE 6/6 NYLON	RED TRANSLUCENT	BRASS	TIN	2–520129–2
MATERIAL	COLOR	MATERIAL	FINISH	PART NO
HOUSING		TERMINAL		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 10/19/89		 TE Connectivity			
		CHK JR RUTH 10/19/89					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D BRATINA 10/19/89		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE ASSEMBLY,ULTRA-FAST FLAG, 6.35 [.250] SERIES	
		1 PLC ± -		108-2043			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± 0.38 [.015]		114-2123		SIZE	
		4 PLC ± -		WEIGHT		CAGE CODE	
		ANGLES ± -		-		DRAWING NO	
MATERIAL		FINISH		A2		RESTRICTED TO	
SEE TABLE		SEE TABLE		00779		-	
				CUSTOMER DRAWING		SCALE	
						8:1	
						SHEET	
						1 of 1	
						REV	
						T	