


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J2	REVISED PER ECO-12-002690	13FEB12	KH	DR

- 1 WIRE INSULATION DIA .115-.170
- 2 BODY FINISH: TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545
- 3 MATERIAL:
 BODY&SLEEVE: COPPER PER ASTM B152
 INSULATION: NYLON, COLOR:BLUE



QTY	DESCRIPTION	PART NO
100	LOOSE PIECE, BOX	8-320862-1
5000	ON TAPE, REEL	2-320862-1
-	LOOSE PIECE	320862

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 13FEB12	STE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK ROHDE DANIEL 13FEB12		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD ROHDE DANIEL 13FEB12	NAME	
0 PLC ± -		PRODUCT SPEC	TERMINAL, P.I.D.G., FLANGED SPADE, WIRE SIZE: 16-14	
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE
2 PLC ± -		WEIGHT	A3	00779
3 PLC ± 0.20[.008]		CUSTOMER DRAWING	DRAWING NO	C-320862
4 PLC ± -		SCALE	8:1	SHEET 1 OF 1
ANGLES ± -		RESTRICTED TO	-	
FINISH		REV	J2	