




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14	G1	REVISED PER ECO-11-004917	11MAR11	RK HMR



AMP WIRE RANGE	RU FILE E13288
22-16 AWG STRANDED	22-16 AWG STRANDED

- 1 WIRE INSULATION DIA.
3.6 MAX
- 2 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - CU PER ASTM B152
INSULATION - NYLON
- 3 FINISH: BODY - TIN PL ASTM B545
SLEEVE - TIN PL ASTM B545
INSULATION - COLOR - RED



---	LOOSE PIECE	165168-0
QTY	PACKAGE TYPE	PART NO

CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 90°C [194°F]
VOLTAGE RATING: -
CIRCULAR MIL AREA: 0.25-1.6mm ² [493-3158] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± 0.38 [.015]
	2 PLC ± 0.20 [.008]
	3 PLC ± -
	4 PLC ± -
MATERIAL	ANGLES ± -
2	FINISH
	3

DWN JR RUTH 16AUG10	STE TE Connectivity			
CHK T MICHELUTTI 16AUG10				
APVD T MICHELUTTI 16AUG10	NAME TERMINAL, WIRE PIN, PIDG WIRE SIZE, 22-16 AWG			
PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
APPLICATION SPEC	A3	00779	C-165168	-
WEIGHT	CUSTOMER DRAWING		SCALE	SHEET
-	6:1		1 OF 1	REV G1