



External Drive Type
(A)

Self Drive Type
(B)

**Conrad
Best.-Nr.**

NO	PART NO	Max Input Voltage	Fr (KHz)	Zr (ΩMAX)	Cp	Dimension(mm)				
						D	d	T	t	
818277	<u>H21205C11</u>	FT-9T-18A1-K882	30Vp-p	18±2	1000	3000PF±30%	Φ9	Φ6	0.22	0.10
818274	<u>H21205C9</u>	FT-12T-6.5A1-K883	30Vp-p	6.5±1.0	800	13000PF±30%	φ12	φ9	0.14	0.08

818273	<u>H21205C8</u>	FT-12T-9.2A1-K884	30Vp-p	9.2±1.0	600	10000PF±30%	φ12	Φ9	0.23	0.10
818289	<u>H21205C25</u>	FT-15T-4.0A1-K885	30Vp-p	4.0±0.5	300	30000PF±30%	Φ15	φ12	0.13	0.07
818285	<u>H21205C22</u>	FT-27G-2.8ASL-886	30Vp-p	2.8±0.5	150	130000PF±30%	φ27	Φ25	0.33	0.10
818278	<u>H21205C14</u>	FT-27G-4.0A1-K887	30Vp-p	4.0±0.5	300	25000PF±30%	φ27	φ20	0.42	0.20
818286	<u>H21205C23</u>	FT-35T-2.9AL-888	30Vp-p	2.9±0.5	1000	30000PF±30%	Φ35	φ25	0.55	0.30
818287	<u>H21205C24</u>	FT-9T-18AL-889	30Vp-p	18±2	2000	3000PF±30%	Φ9	Φ6	0.22	0.10