

Product information

95 61 150

Bowden Cable Cutter

- For Bowden cables and soft wire rope up to Ø 3.0 mm (also V2A)
- Smooth and clean cutting due to special shape of the cutting edges
- Sickle shape cutting edges surround the material and prevent the wire rope fanning out
- Little handforce required due to very high transmission ratio
- With opening spring and locking device



///

General

Article No.	95 61 150
EAN	4003773065197
Shears	black atramentized
Head	polished
Handles	plastic coated
Weight	205 g
Dimensions	150 x 60 x 20 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacity copper cable, fine-stranded (diameter)	Ø 3 mm
Cutting capacities wire rope (diameter)	Ø 3 mm

technical change and errors excepted

