

## Product information

# 00 21 20 LE

## Tool Case "Vision24"

Empty



- With a total of 21 inserting options
- Max. payload: 20 kg
- Volume: 24 litres
- Without tools
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the bottom side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- Dimensions, exterior (W x H x D): 480 x 380 x 200 mm; dimensions, interior (W x H x D): 460 x 310 x 190 mm

### General

|                 |                       |
|-----------------|-----------------------|
| Article No.     | 00 21 20 LE           |
| EAN             | 4003773044567         |
| Weight          | 4,485 g               |
| Dimensions      | 370 x 173 x 360 mm    |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

### Technical details

|                                         |                 |
|-----------------------------------------|-----------------|
| Dimension exterior (interior) width mm  | 480 mm (460 mm) |
| Dimension exterior (interior) height mm | 180 mm (170 mm) |
| Dimension exterior (interior) depth mm  | 370 mm (310 mm) |

*technical change and errors excepted*

*Con-Pearl® is a registered trade mark of friedola TECH GmbH*