

Product information

98 07 250

- Parallel smooth gripping jaws
- Variable gripping width
- With scaling for presetting the width apart from the workpiece

Adjustable Wrench

IEC 60900 DIN EN 60900



⚡ 1000 V  $\angle 22^\circ$

General

Article No.	98 07 250
EAN	4003773071518
Handles	with dipped insulation
Weight	545 g
Dimensions	260 x 78 x 32 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw width	8 mm
Head width (W3)	16 mm
Depth	20 mm
Width	73 mm
Capacities for nuts	30 mm
Capacities for nuts	1 1/8

technical change and errors excepted

