

## Product information

# 16 40 150

## Stripping Tool

- For dismantling round cables exceeding Ø 25.0 mm
- Removes all sheaths of standard cables
- Suitable for longitudinal and circular cutting
- Cutting depth can be adjusted up to 5.0 mm
- Replaceable blade (both sides can be used)



### General

|                 |                                  |
|-----------------|----------------------------------|
| Article No.     | 16 40 150                        |
| EAN             | 4003773026709                    |
| Handles         | glass fibre reinforced polyamide |
| Weight          | 210 g                            |
| Dimensions      | 150 x 53 x 28 mm                 |
| REACH compliant | does not contain SVHC            |
| RoHS compliant  | not applicable                   |

### Technical details

|                                 |           |
|---------------------------------|-----------|
| Stripping capacities (diameter) | Ø > 25 mm |
|---------------------------------|-----------|

*technical change and errors excepted*



Setting the tool for longitudinal cut



Longitudinal cut



Turning the tool for circumferential cut



Circular cut



Adjustable cutting depth