

Product information

95 05 165

Cable Shears

Handles extrusion plastic-coated



MM

- Cuts cables up to Ø 10 mm / 24 mm²
- With opening spring and locking device
- Blades made of stainless steel
- Oil-hardened and tempered
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- No crushing, slight deformation of the cable only
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint

General	
Article No.	95 05 165
EAN	4003773019596
Head	polished
Handles	plastic coated
Weight	111 g
Dimensions	165 x 48 x 16 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded	24 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 10 mm
AWG	4

technical change and errors excepted