

Product information

97 22 240

Crimping Pliers

- For cutting cables, stripping wire and crimping insulated terminals and heat shrinkable sleeve connectors and non-insulated plug type connectors
- With threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- Bolted joint for higher stability and even movement



General

Article No.	97 22 240
EAN	4003773070726
Pliers	black lacquered
Handles	with multi-component grips
Weight	270 g
Dimensions	240 x 62 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	insulated terminals + cable connectors
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimp profiles	3
AWG	20 — 10

technical change and errors excepted