

## Product information

# 00 21 15

### Tool Box

7 parts

For electrical contractors

- All pliers and screwdrivers except water pump pliers VDE-tested according to DIN EN/IEC 60900
- High-quality, versatile, shock-resistant plastic case
- Foam insert with honeycomb structure for variable equipment
- External dimensions (W x H x D): 340 x 56 x 275 mm



### General

|                 |                       |
|-----------------|-----------------------|
| Article No.     | 00 21 15              |
| EAN             | 4003773042853         |
| Weight          | 1,520 g               |
| Dimensions      | 325 x 270 x 54 mm     |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

### Content

|           |                                                                                                                                                                                                                                                             |
|-----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 03 06 180 | 1 x Knipex Combination Pliers (180 mm)<br>⚡ 1000V                                     |
| 26 16 200 | 1 x Knipex Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm)<br>⚡ 1000V   ⊖ |
| 70 06 160 | 1 x Knipex Diagonal Cutter (160 mm)<br>⚡ 1000V                                                                                                                           |
| 88 03 180 | 1 x Knipex KNIPEX Alligator® Water Pump Pliers (180 mm)<br>                                                                                                              |
| 006100    | 1 x Wera Screwdrivers for slotted screws 160 i (0,4 x 2,5 x 80 mm)<br>⚡ 1000V ⊖                                                                                                                                                                             |
| 006115    | 1 x Wera Screwdrivers for slotted screws 160 i (0,8 x 4,0 x 100 mm)<br>⚡ 1000V ⊖                                                                                                                                                                            |
| 006152    | 1 x Wera Screwdrivers for cross recessed Phillips® screws 162i PH (PH1 x 80 mm)<br>⚡ 1000V ⊕                                                                                                                                                                |

technical change and errors excepted