

Product information

92 08 78 ESD

SMD Precision Tweezers

DIN EN 61340 -5-1



- When working on SMD components (SMD = surface mounted device): the fine geometry of the SMD tweezers also allows work to be carried out on electronic components that can be soldered directly onto the circuit board using solderable connecting surfaces
- Handcrafted: polished edges and an excellent matt, scratch-free and non-reflective surface
- For assembly work, laboratory processes, clean room environments, circuit board repairs and reworking in the electronics industry
- High-quality premium stainless steel: high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Antimagnetic to avoid electromagnetic damage
- The variety of designs and jaw types enables small components to be held, positioned and controlled securely in confined spaces
- This allows to compensate in a controlled manner the differences in potential between the operator and electronic components
- With a tested black epoxy resin coating with a surface resistance between 10^4 and 10^9 ohms

General

Article No.	92 08 78 ESD
EAN	4003773054634
Material	stainless steel
Gripping surfaces	smooth gripping surfaces
Handles	Smooth
Weight	15 g
Dimensions	118 x 10 x 12 mm
Standard	DIN EN 61340 -5-1
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Surface	matt finish
Finish	angled 45°
Tips width (A)	0.5 mm
Tips width (B)	2.5 mm
Tweezers tip version	positioning
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	yes
VDE tested	no
Sectors	electronics
Magnetic	non-magnetisable (80%)
Behaviour	electrically dissipative

technical change and errors excepted