

Product information

92 22 35

Universal Tweezers



- Universal Tweezers are suitable for demanding standard applications and precision tasks
- Wide range of designs: straight, angled, gripping surfaces and handles smooth or serrated, with needle points, narrow or blunt tips, as well as different lengths
- For the electronics industry, watchmakers and jewellers
- High-quality stainless steel: extremely tough and very good corrosion resistance against a variety of atmospheric environments and many corrosive materials

General

Article No.	92 22 35
Reference number	648.SA.B
EAN	4003773054719
Material	stainless steel
Gripping surfaces	knurled gripping surfaces
Handles	serrated
Weight	25 g
Dimensions	155 x 8 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Surface	matt finish
Finish	straight
Tips width (A)	0.5 mm
Tips width (B)	0.5 mm
Tweezers tip version	pointed
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	no
VDE tested	no
Sectors	Industry electronics Watch makers Jeweller
Magnetic	non-magnetisable (80%)
Behaviour	Conductive

technical change and errors excepted