

Product information

92 58 74 ESD

Universal Tweezers ESD

DIN EN 61340 -5-1



- For secure handling of electronic workparts: equalize differences in electrical potential between their user and the workpieces in a controlled manner
- ESD-tested, black epoxy resin coating with a surface resistance between 10^3 and 10^9 ohms
- For the electronics and precision engineering industries
- Antimagnetic to avoid electromagnetic damage
- Wide range of designs: straight, angled, gripping surfaces and handles smooth or serrated, with needle points, narrow or blunt tips
- The high quality stainless steel ensures extreme toughness and very good corrosion resistance against a variety of atmospheric environments and many corrosive materials
- Also available as a set (92 00 01 ESD)

General

Article No.	92 58 74 ESD
Reference number	2A.SA.NE.B
EAN	4003773054900
Material	stainless steel
Gripping surfaces	smooth gripping surfaces
Handles	Smooth
Weight	16 g
Dimensions	118 x 10 x 12 mm
Standard	DIN EN 61340 -5-1
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Surface	matt finish
Finish	straight
Tips width (A)	0.3 mm
Tips width (B)	2 mm
Tweezers tip version	blunt
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	yes
VDE tested	no
Sectors	electronics
Magnetic	non-magnetisable (80%)
Behaviour	electrically dissipative

technical change and errors excepted