

Product information

98 20 55

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling

Screwdrivers for slotted screws

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General

Article No.	98 20 55
EAN	4003773024224
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	69 g
Dimensions	232 x 28 x 29 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Blade length	125 mm
Length of non-insulated blade	15 mm
Handle length	107 mm
Blade width	5.5 mm
Blade thickness	1.0 mm
VDE tested	yes

technical change and errors excepted