

## Product information

# 98 24 02

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling

## Screwdriver for cross recessed screws

Phillips®

IEC 60900 DIN EN 60900



⚡ 1000V ⊕

### General

|                 |                                               |
|-----------------|-----------------------------------------------|
| Article No.     | 98 24 02                                      |
| EAN             | 4003773026457                                 |
| point           | burnished                                     |
| Handles         | insulating multi-component handle, VDE-tested |
| Weight          | 94 g                                          |
| Dimensions      | 212 x 33 x 35 mm                              |
| Standard        | DIN EN 60900 IEC 60900                        |
| REACH compliant | does not contain SVHC                         |
| RoHS compliant  | not applicable                                |

### Technical details

|                               |        |
|-------------------------------|--------|
| Size                          | PH2    |
| Blade length                  | 100 mm |
| Handle length                 | 112 mm |
| Blade Ø                       | 6.0 mm |
| Length of non-insulated blade | 18 mm  |
| VDE tested                    | yes    |

*technical change and errors excepted*

*Phillips® is a registered trademark of Phillips Screw Company*