



**PRODUCT NUMBER: 2232255**

**PERFECT POLY®**

Handling of fine products in a dry or slightly greasy or soiled environment. Assembly, automotive industry assembly, logistics (forklift operators), sorting of parts.

**Honeywell**

**Overview**

**Reference Number**

2232255

**Product Type**

Gloves

**Range**

General purpose

**Line**

Precision work

**Brand**

Honeywell

**Brand formerly known as**

SPERIAN

**Industry**

- Automotive and Part Manufacturer
- Aviation
- Building and Construction
- Energy or Electricity
- Logistics
- Maintenance
- Services
- Telecoms
- Transportation
- Utilities

**Product Use**

Handling of fine products in a dry or slightly greasy or soiled environment. Assembly, automotive industry assembly, logistics (forklift operators), sorting of parts.

**Features & Benefits**

**Feature**

White polyamide knitted glove  
White polyurethane coating on palm and fingertips

**Benefit**

COMFORT  
The knitting technique helps to obtain a glove that conforms snugly to the hand, with good dexterity. The glove offers maximum comfort and added sturdiness. The tight knit gives the glove perfect support, limits the penetration of dirt and offers a good touch. The ventilated back and PU coating optimise the glove's breathability.

**RESISTANCE**

Polyamide with its polyurethane coating provide excellent abrasion and tear resistance. The PU coating ensures a good grip.

**SAFETY**

Non pilling, the polyamide is suitable for precision work.  
The gloves are certified as "silicone-free" to ensure their use in painting environment.

**HYGIENE**

Its white colour enhances the glove's hygiene and cleanliness.

**Technical Description**

**Description**

CE CATEGORY : II Intermediary risks  
In accordance with standards :  
EN 420:2003 + A1:2009 Basic standards  
EN 388:2016 Mechanical hazards

**CHARACTERICS :**

White polyamide knitted glove  
White polyurethane coating on palm and fingertips

**Product Technology**

Knitted Coated

**Gauge**

15

**Glove/liner color**

White

**Coating Type**

Polyamide and polyurethane

**Length**

24 cm

**Harmlessness**

In conformity with the European standards.

**Dexterity**

Class 5

**Sizes**

6 to 11

**EN 388 - Mechanical Hazards Abrasion Resistance**

Abrasion resistance	3
Cutting resistance (Coupe test)	1
Tear resistance	3
Puncture resistance	1

**Packaging Label**

**Tagging**

CE HONEYWELL  
2232255 XX  
EN 420  
EN 388 : 3131

**Certifications**

E.C. Declaration of Conformity

**EC Category PPE**

2

**Quality Assurance**

ISO 9001 / 2000

**EU Certificate Number**

0075/797/162/05/18/0797

**EC Attestation**

EC Attestation

**EC Attestation Number**

0075/797/162/05/18/0797

## Additional Information

**User Manual**

UI 102

**User Information Sheet**

102

## Maintenance

**Storage Information**

Minimum packaging : 10 pairs.

Cartons of 100 pairs.

**Care Instructions**

This article can be cleaned. For cleaning instructions, please contact Honeywell Safety Products.