

GARRETT ACE 150 METAL DETECTOR



With the quality and performance of the ACE 150, you can begin finding treasure right away—in your own backyard or wherever you travel.

Easy to use for any age!

Model No. 1138070 MSRP: \$179.95

KEY FEATURES | TECH SPECS | SEARCHCOILS | ACCESSORIES

ACE 150 SPECIFICATIONS AND SETTINGS

- Length: 42" to 51" - (1.06m - 1.29m), Adjustable
- Arm Cuff, Adjustable
- Weight: 2.7 lbs. (1.2 kgs.)
- Frequency - 6.5 kHz
- 4 AA Battery Operation (Batteries Included)
- 2 year Warranty, Limited Parts/Labor

Settings:

- Sensitivity / Depth Adjustments (4 settings)
- Mode, 3 Distinct Discrimination Patterns

Design features and specifications are subject to change without notice.



Related Links

- Owner's Manual
 - English
 - Spanish
- Detector Selector
- Product Reviews



Watch **ACE 150** Video



- **The ACE 150 is packed with features** normally only found on a metal detector which costs much more.
- **One-Touch™ treasure hunting**—Power on the detector with the touch of a button and the ACE 150 is ready to search!
- **Three search mode options:** All-Metal, Jewelry and Coins modes.
- **Graphic Target ID Cursor** has 5 segments of notch discrimination to eliminate unwanted targets.
- **Three-Level Tone ID** to audibly distinguish targets.
- **Coin depth indicator**—The depth of a coin is shown on the ACE 150's LCD screen with depths highlighted as either 2", 4" or 6"+.
- **Lightweight and adjustable**—The ACE 150 weighs only 2.7 pounds (1.2 kgs.). Search stem length can be adjusted from 42" (1.06 m) to 51" (1.29 m) to accommodate different user heights.
- **Includes Owner's Manual and Instructional DVD.**