

Conrad Artikelnummer	Hersteller Teilenummer	PRODUCT NAME	COLOUR TEMPERATURE	CONSTRUCTION	PRODUCT NET WEIGHT	VOLTAGE	LIGHTING ANGLE	POWER CONSUMPTION	LM	LIFE SPAN	Abmessung
841204	13520	LED BULB	6000-8000K	LED/PCB	1.2g*2	DC 12-14V	120 degree	2W	20	20000h	L 2,4cm/ Breite bzw. Ø 0,9cm
841206	13521	LED BULB	Wave length : 460-465nm	LED/PCB	1.2g*2	DC 12-14V	120 degree	2W	16	20000h	L 2,4cm/ Breite bzw. Ø 0,9cm
841207	13522	LED BULB	6000-8000K	LED/PCB	3.0g*2	DC 12-14V	240 degree	1.2W	160	20000h	L 4,5cm/ Breite 1,1cm / Höhe 0,5cm
841208	13523	LED BULB	Wave length : 460-465nm	LED/PCB	3.0g*2	DC 12-14V	240 degree	1.2W	128	20000h	L 4,5cm/ Breite 1,1cm / Höhe 0,5cm
841209	13524	LED BULB	6000-8000K	LED/PCB/T5 BASE	0.8g*2	DC 12-14V	120 degree	0.3W	6	20000h	L 1,8cm/ Breite bzw. Ø 0,5cm
841210	13525	LED BULB	Wave length : 460-465nm	LED/PCB/T5 BASE	0.8g*2	DC 12-14V	120 degree	0.3W	4,8	20000h	L 1,8cm/ Breite bzw. Ø 0,5cm
841211	13526	LED BULB	Wave length : 622-627 nm	LED/PCB/T5 BASE	0.8g*2	DC 12-14V	120 degree	0.3W	4,8	20000h	L 1,8cm/ Breite bzw. Ø 0,5cm
841212	13527	LED BULB	6000-8000K	LED/PCB/BA9S BASE	2.4g*2	DC 12-14V	360 degree	1.4W	100	20000h	L 3,1cm/ Breite bzw. Ø 1,3cm
841213	13528	LED BULB	Wave length : 460-465nm	LED/PCB/BA9S BASE	2.4g*2	DC 12-14V	360 degree	1.4W	80	20000h	L 3,1cm/ Breite bzw. Ø 1,3cm
841214	13529	LED BRAKE LIGHT	6000-8000K	LED/PCB/BA15S BASE	9.4g	DC 12-14V	360 degree	3.7W	260	20000h	L 4,3cm/ Breite bzw. Ø 2,0cm
841216	13530	LED BRAKE LIGHT	Wave length : 622-627 nm	LED/PCB/BA15S BASE	9.4g	DC 12-14V	360 degree	3.7W	208	20000h	L 4,3cm/ Breite bzw. Ø 2,0cm
841219	13531	LED BRAKE LIGHT	6000-8000K	LED/PCB/BA15D BASE	10.2g	DC 12-14V	360 degree	5W	360	20000h	L 4,3cm/ Breite bzw. Ø 2,0cm
841221	13532	LED BRAKE LIGHT	Wave length : 622-627 nm	LED/PCB/BA15D BASE	10.2g	DC 12-14V	360 degree	5W	288	20000h	L 4,8cm/ Breite bzw. Ø 2,0cm
841222	13533	LED BULB	6000-8000K	LED/PCB/3157 BASE	9.9g	DC 12-14V	360 degree	4.5W	340	20000h	L 4,5cm/ Breite bzw. Ø 2,1cm
841223	13534	LED BULB	Wave length : 622-627 nm	LED/PCB/3157 BASE	9.9g	DC 12-14V	360 degree	4.5W	272	20000h	L 4,5cm/ Breite bzw. Ø 2,1cm