

| | | |
|-----------------------|-----------------------|--|
| Rating | DC12V/24V 25mA/10mA | <p style="text-align: center;">Circuit Diagram</p> |
| Insulation Resistance | DC 500V 100M ohm Min. | |
| Dielectric Strength | AC 1000V 1 minute | |
| Operation Temperature | -20°~+60°C | |
| LED Type | 2000med White | |
| LED Life | 10000hrs | |
| CCT | 17671K±20% | |
| Max Illuminance | DC12V 30.50 Lux±20% | |

