



Light is style  
COOL BLUE<sup>®</sup> INTENSE

Light is OSRAM

**OSRAM**

### Main benefits of COOL BLUE® INTENSE

- Bluish-white light for xenon look
- Color temperatures up to 4,200 K
- Up to 20% brighter<sup>1)</sup>
- Modern design with silver cap (H4, H7, H11, H27W/1, H27W/2, HB4)
- Ideal for use in clear-glass headlights
- W5W with color temperatures up to 3,700 K (± 200 K)
  - More homogeneous color appearance in combination with HID-systems
  - For interior lighting/parking light/license plate illumination, interchangeable with standard bulbs



### OSRAM COOL BLUE® INTENSE

Order number	ECE	V	W	Base
64150CBI	H1	12	55	P14.5s
64150CBI-01B	H1	12	55	P14.5s
64150CBI-HCB	H1	12	55	P14.5s
64151CBI	H3	12	55	PK22s
64193CBI	H4	12	60/55	P43t
64193CBI-01B	H4	12	60/55	P43t
64193CBI-HCB	H4	12	60/55	P43t
64210CBI	H7	12	55	PX26d
64210CBI-01B	H7	12	55	PX26d
64210CBI-HCB	H7	12	55	PX26d
64212CBI-HCB	H8	12	35	PGJ19-1
64211CBI	H11	12	55	PGJ19-2
64211CBI-HCB	H11	12	55	PGJ19-2
64176CBI	H15	12	55/15	PGJ23t-1
64176CBI-HCB	H15	12	55/15	PGJ23t-1
64219CBI	H16	12	19	PGJ19-3
64219CBI-HCB	H16	12	19	PGJ19-3
880CBI	H27W/1	12	27	PG13
881CBI	H27W/2	12	27	PGJ13
9005CBI-HCB	HB3	12	60	P20d
9006CBI-HCB	HB4	12	51	P22d
9012CBI	HIR2	12	55	PX22d
2825HCBI	W5W	12	5	W2.1x9.5d
2825HCBI-02B	W5W	12	5	W2.1x9.5d

1) Compared with standard lamps, subjective perception

**OSRAM COOL BLUE® INTENSE**

Order number	EAN10 WEST-MEA	EAN10 CIS	EAN10 EASTIC	EAN10 LATAM	EAN10 APAC
64150CBI	4008321655325	4008321655325	4008321655325	4008321655325	4008321655325
64150CBI-01B	4008321655424	4052899411418	4052899411432	4052899411395	-
64150CBI-HCB	4008321650719	4052899412880	4052899412965	4052899412804	4008321660329
64151CBI	4008321655462	4008321655462	4008321655462	4008321655462	4008321655462
64193CBI	4008321650894	4008321650894	4008321650894	4008321650894	4008321650894
64193CBI-01B	4008321651280	4052899410794	4052899410817	4052899410718	-
64193CBI-HCB	4008321650733	4052899413061	4052899413108	-	4052899413122
64210CBI	4008321651341	4008321651341	4008321651341	4008321651341	4008321651341
64210CBI-01B	4008321651563	4052899410831	4052899410855	-	-
64210CBI-HCB	4008321650757	4052899413047	4052899413085	-	4008321660367
64212CBI-HCB	4052899931077	4052899412903	4052899412989	4052899412828	4052899487130
64211CBI	4052899433175	4052899433175	4052899433175	4052899433175	4052899433175
64211CBI-HCB	4008321650771	4052899412927	4052899413009	4052899412842	4008321660404
64176CBI	4052899932708	4052899932708	4052899932708	4052899932708	4052899932708
64176CBI-HCB	4052899982208	4052899982192	4052899982185	-	-
64219CBI	4052899268326	4052899268326	4052899268326	4052899268326	4052899268326
64219CBI-HCB	4052899268357	4052899412941	4052899413023	4052899412866	-
880CBI	4052899479999	4052899479999	4052899479999	4052899479999	4052899479999
881CBI	4052899480025	4052899480025	4052899480025	4052899480025	4052899480025
9005CBI-HCB	4008321660282	4052899413641	4052899413726	4052899413566	4008321660428
9006CBI-HCB	4008321660305	4052899413665	4052899413740	4052899413580	4008321660442
9012CBI	4052899455405	4052899455405	4052899455405	4052899455405	4052899455405
2825HCBI	4008321650849	4008321650849	4008321650849	4008321650849	4008321650849
2825HCBI-02B	4008321650870	4052899418646	4052899418660	4052899418622	4008321650870

**OSRAM GmbH**

Head office:

Marcel-Breuer-Strasse 6  
 80807 Munich, Germany  
 Phone +49 89 6213-0  
 Fax +49 89 6213-2020  
 www.osram.com

