

Technical Data Sheet

Cord / Cordless Hair Clipper



General Data:

Type Range.... Grooming
 Warranty..... 3 Years

Included Accessories

2 combs with 15 lock-in-length settings (1-42 mm)

Available Spare Part

NA

Application

Hair Clipper

Mechanical Data

Length 185mm
 Width 45mm
 Height 40mm
 Weight 248g
 Housing material ABS
 Housing colour Black

Functional Features

Fixed blade_material 420 J2 SS
 Fixed blade thickness 1.8mm
 Moving blade_material 420 J2 SS
 Moving blade thickness 1.2mm

Washable No
 Date Code: On the rating plate

VKB **EAN**
 43129560100 4008496652341

Electrical Data:

Power supply voltage..... 220-240Vac, 50/60Hz
 Input power..... 7W
 Rechargeable battery..... 2 x "AAA", 730mAh, NiMH Batteries
 Charging time..... 16Hours
 Quick charge No
 Max run time in case of battery operation..... 30mins
 Cord length..... 1.83
 Power consumption..... 5W
 Motor speed..... 6700+/-1000rpm
 Noise level in operation..... 78dB
 Plug..... EU

Protective Functions:

Overcharge protection..... no
 Short circuit protection..... yes

Temperature Range:

Operating temperature..... 15°C – 35°C
 Storage temperature..... <= 60 °C
 Charging temperature..... 15°C – 35°C

Indications:

Charge control LED..... One LED
 Rest capacity display..... No