

FOR A GOOD REASON
GRUNDIG



Ionic Hair dryer HD 6080

Product data

- 2200 W output max.
- 3 temperature settings: gentle, environmentally-friendly energy-saving mode, as well as turbo setting.
- 2 speed settings
- Cool Shot solidifies and stabilizes the hair.
- Ionic function:
For anti-static, smooth, shiny hair. Keeps vitality and bounce in your hair and hydrates the hair structure in a natural way.
- Detachable air inlet grille
- Small styling nozzle
- Cable with hanging loop
- Mains operation 230-240 V~, 50 Hz
- Color: highgloss black / silver



6 heat- and speed settings



Model number	HD 6080
Order number	GMN 0400
Packaging unit	6
Bar code	4013833622801
RRP	