



Hair and Beard Clipper MC 6040

Product data

- Mains and rechargeable operation
- Ca. 45 minutes cordless operation
- Worldwide automatic voltage adjustment 100 - 240 V~, 50/60 Hz
- 1 blue LED charging indication
- Powerful motor
- Washable, hygienic cutting head
- High-quality and maintenance-free ceramic blade for a clean and precise cut
- Cutting width: 40 mm
- Cutting length: 1,5 - 41 mm
- Convenient telescopic comb system for hair and beard cutting with 20 settings:
 - No 1: 2, 4, 6, 8, 10, 12, 14, 16, 18, 21 mm
 - No 2: 22, 24, 26, 28, 30, 32, 34, 36, 38, 41 mm
- Display of cutting lengths
- Precise trimming grade lock during use
- High-quality soft-touch finish
- Accessories: 2 telescopic combs (for hair and beard), charging and storage stand, small plug and cleaning brush
- Colour: glossy grey / black



Ceramic blade



Large telescopic comb 2 - 21 mm



Small telescopic comb 22 - 41 mm



Model number	MC 6040
Order number	GMM 3810
Packaging unit	6
Bar code	4013833623649
RRP	59,99 €