

## Data Sheet

## Premium LED Light 3AAA

17634



<b>Designation:</b>	<b>17634 101 421</b>
Battery Requirement:	3 x AAA
Bulb required:	Taiwanese Profi Light LED
Luminous intensity:	30 lumens or 325 cd
Range:	36m (calculated distance at maximum luminous intensity with an illuminance of 0.25lux)
Weight:	81g (without batteries)

<b>Material:</b>	Aluminum (Anodized)
	ABS (Acrylonitrile Butadiene Styrene)
	PC (Polycarbonate)
	All contact parts made of aluminum or steel
	Contact spring nickel or Zinc plated steel

<b>Dimensions (mm):</b>	<b>A</b>	<b>114</b>
	<b>B</b>	<b>37.9</b>
	<b>C</b>	<b>32</b>
	<b>D</b>	<b>26.7</b>

**Run Time: 13 hours (with VARTA alkaline battery)**

### Features (Technical)

- Push switch (on/off)
- 9 feet impact resistant
- Water resistant