

Data Sheet

Indestructible 5pcs 5mm LED Headlight 3AAA

17730



Designation:	17730 101 421
Battery Requirement:	3x AAA
Bulb required:	5pcs 5mm cool white LED
Luminous intensity:	High: 35 lumens or 150 cd Low: 11 lumens or 58 cd
Range:	24m High / 15m Low (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)
Weight:	64g (without batteries)

Material:	PP (Polypropylene) ABS (Acrylonitrile Butadiene Styrene) PC (Polycarbonate) TPR (Thermoplastic Rubber) All contact parts made of bronze or nickel plated steel
------------------	--

Dimensions (mm):	A	60
	B	40

Run Time: High: 19 hours (with VARTA HE)
Low: 40 hours (with VARTA HE)

Features:

- 30 feet drop test
- 5pcs super bright 5mm cool white LED
- MCU control push switch (High/Low/Off)
- PC material body with over-mould rubber head for maximum durability
- Lighting leakage design when forget to turn off switch
- Compact and lightweight headlight
- 60° pivoting head
- Magnifier lens provide
- Passed extreme temperature shock test
- IPX4 water resistant
- 10,000 Switch cycle life