

## Data Sheet

## Indestructible 1W LED Headlight 3AAA

17731

**Designation:** 17731 101 421

**Battery Requirement:** 3x AAA

**Bulb required:** CREE XPC Q5 cool white

**Luminous intensity:** High: 100 lumens or 2500 cd  
Low: 36 lumens or 920 cd

**Range:** 100m High / 60m Low (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)

**Weight:** 65g (without batteries)

**Material:**

PP (Polypropylene)

PC (Polycarbonate)

TPR (Thermoplastic Rubber)

All contact parts made of bronze or nickel plated steel

**Dimensions (mm):**

A	60
B	40

**Run Time: High: 3 hours (with VARTA HE)**

**Low: 15 hours (with VARTA HE)**

**Features:**

30 feet drop test

Super bright CREE cool white LED

MCU control push switch (High/Low/Off)

PC material body with over-mould rubber head for maximum durability

Lighting leakage design when forget to turn off switch

Compact and lightweight headlight

60° pivoting head

Passed extreme temperature shock test

IPX4 water resistant

10,000 Switch cycle life

