

reflecta CrystalScan 7200



This scanner is the ideal device for **high-resolution digitalization** of your slides and negatives. The scanner is equipped with **7200x3600 dpi** permitting extremely high-quality print production up to A4 size. Therefore the fast scanning speed and the **Digital ICE³™** – **hardware dust and scratch removal** - enables the user an effective working.

- **Digital ICE-** hardware based dust- and scratch removal with infrared sensors and automatical software correction
- **Digital ROC** – color restoration
- **Digital GEM** – grain management

Product Information

- **Film Type:** Negative and Positive as strip (35mm) or slide (5x5cm)
- **Optical Resolution:** 7200x3600 dpi
- **Color Depth:** 48 Bit
- **Image Sensor:** tri-linear CCD
- **Light Source:** LED
- **Scanning Time:**
Scan at 1800dpi 35 Sec.
- **Scan Area max:** 24,3 x 36,5 mm
- **Interface:** USB 2.0

Technical Details

- **Weight:** 1,0 kg
- **Dimension:** 278 x 169 x 70 mm
(L x W x H)
- **Power Supply:** Power adaptor
- **System Requirements:**
PC: Pentium III or higher, with at least 512 MB RAM, Windows XP, Vista, 7, 8, 10 (32/64 bit)
MAC: Mac OS X 10.5 or higher

Delivery Content:

- Scansoftware Cyberview X
- Power adaptor, USB Cable
- User manual

Art.No. 65380
EAN: 4005039653803

Specifications are subject to change without prior notice.



reflecta gmbh

Merkurstraße 8

D-72184 Eutingen im Gäu

Phone: +49 (0) 7457 9465-60

Fax: +49 (0) 7457 9465-72

e-mail: mail@reflecta.de

http: www.reflecta.de