

Programming Quick Guide - LS6300E

Installation


Make sure that the scanner has the correct cable to plug in the PC as below described::

USB cable Connection: / PS2 cable connection

(Please use correct cable for the interface)

Reset Configuration to Defaults

If you are unsure of the scanner configuration or have scanned the incorrect codes, please scan the “Set Factory default” barcode. This will reset the scanner to its factory defaults.



Default

***Please remove the protective sticker from window before use.**



<u>Indicator Information</u>	
Red LED ON	Not read
Green LED	Good read

OUTPUT MODE –
KEYBOARD / USB



SINGLE SCAN



LASER TIMEOUT
-5 SECONDS



CODE 11 DOUBLE
CHECK - ENABLE




CODE 39 DOUBLE
CHECK ENABLE



CODE 93 DOUBLE
CHECK - ENABLE




CODE 128 DOUBLE
CHECK - ENABLE




OUTPUT
MODE

READING
MODE

SINGLE SCAN NO
TRIGGER




LASER TIMEOUT
-2 SECONDS




DOUBLE
CHECK

CODE 11 DOUBLE
CHECK - DISABLE




CODE 39 DOUBLE
CHECK DISABLE




CODE 93 DOUBLE
CHECK - DISABLE




CODE 128 DOUBLE
CHECK - DISABLE



I2OF5 DOUBLE
CHECK - ENABLE



ID2OF5 DOUBLE
CHECK - ENABLE



MSI DOUBLE
CHECK - ENABLE




UPC/EAN DOUBLE
CHECK ENABLE




REVERSE IMAGE
- ENABLE



SEND BAR CODE
ID - DISABLE



SEND BAR CODE
ID - RESET



DOUBLE
CHECK


I2OF5 DOUBLE
CHECK - DISABLE



ID2OF5 DOUBLE
CHECK - DISABLE



MSI DOUBLE
CHECK - DISABLE



UPC/EAN DOUBLE
CHECK DISABLE




REVERSE IMAGE
- DISABLE



SEND BAR CODE
ID - AS A PREFIX



SEND BAR CODE
ID - AS A SUFFIX




IMAGE

CODE ID

Keyboard Language


DENMARK




FINLAND




FRANCE




GERMANY




ITALY



LATIN AMERICA




NETHERLANDS




NORWAY




POLAND




SPAIN




SWITZERLAND
(FRENCH)




SWITZERLAND
(GERMAN)




SWEDEN




UNITED KINGDOM



UNIVERSAL



UNITED STATES



Symbologies On/OFF-1

CODE 11 –
ENABLE




CODE 11

CODE 11 –
DISABLE



CODE 39 –
ENABLE



CODE 39

CODE 39 –
DISABLE



FULL ASCII –
ENABLE



FULL ASCII –
DISABLE



CODE 93
-ENABLE




CODE 93

CODE 93
-DISABLE



CODE 128
-ENABLE



CODE 128

CODE 128 –
DISABLE



CODE 128 ISBT -
ENABLE



CODE 128 ISBT -
DISABLE




CODABAR –
ENABLE




CODABAR

CODABAR -
DISABLE




Symbologies On/OFF-2

I2OF5 - ENABLE



INTERLEA
VED 2 OF 5

I2OF5 - DISABLE




ID2OF5 - ENABLE



INDUSTRIAL
2 OF 5

ID2OF5 - DISABLE




MSI - ENABLE



MSI

MSI - DISABLE



UPC-A ENABLE




UPC/EAN

UPC-A DISABLE



UPC-E ENABLE




UPC-E DISABLE



EAN-13 ENABLE



EAN-13 DISABLE



EAN-8 ENABLE



EAN-8 DISABLE

